



TECHNICAL INFORMATION

BEST-CA 244

BEST-CA 244 is a one-component, solvent free cyanoacrylate adhesive based on ethyl-cyanoacrylate.

BEST-CA 244 is the standard product for bonding of plastics, e.g. polyamide, PVC, PMMA, and various elastomers, e.g. rubber, EPDM and Viton amongst each other and with metals and ceramics. Due to the high viscosity the product is specially designed for bonding of porous surfaces as well as working overhead and on vertical or sloped surfaces.

BEST-CA 244 is very fast cure. After full cure the adhesive is high strength and temperature resistant.

BEST-CA 244 is ready-to-use and can be applied from the original container.

BEST-CA 244 is applied spot-wise or bead like. Assemble parts by using short, firm pressure. Curing process starts within seconds. On most materials fixture time is reached within 15 to 25 seconds. 85 % of final cure is reached after 30 minutes, 100% after 20 hours. The rate of cure depends on the ambient relative humidity. A relative humidity of 40 to 60% will lead to best results. Lower values may delay cure.

Bonding surfaces must be dry, free of dust and grease as well as other contaminants. Sand-blasting, grinding and staining bonding surfaces will enhance adhesion on bonding surfaces.

PROPERTIES (liquid product)

Chemical type	Ehyl-cyanoacrylate
Curing system	Humidity
Appearance	Colourless to yellowish
Viscosity (Brookfield)	Gel
Density (DIN 51757)	1,09 x 10 ³ kg/m ³
Max. gap filling	0,30 mm
Shelf life <small>(Storage in unopened original container at 10°C up to 23°C)</small>	6 months
<u>Curing time @23°C</u>	
Fixture time	15 to 25 seconds
Functional strength	30 minutes
Final strength	20 hours



STRENGTH VALUES (cured product)

Tensile shear strength (DIN 53283) 17 N/mm²

TEMPERATURE RANGE

short-term exposure 120°C
long-term exposure 100°C

CHEMICAL AND ENVIRONMENTAL RESISTANCE

BEST-CA adhesives show good resistance to changing climatic conditions and chemical influences.

HEALTH AND SAFETY STANDARDS

Cyanoacrylate. Danger! Adheres skin and lids within seconds. Keep product out of reach of children. Vapour irritates mucous membranes. Ensure proper ventilation. For constant or long term use vapour extraction is recommended. For further information please see corresponding EG-material safety data sheets.

General

The data and information above correspond to the current know-how of BEST-Klebstoffe GmbH & Co.KG. Our information and data have been developed from laboratory tests and extensive practical experience. It is the user's responsibility to perform receiving inspections and to determine suitability for the user's purpose of any production methods. We disclaim all warranties expressed or implied, that any product will have specific properties for a particular purpose. BEST-Klebstoffe GmbH & Co. KG reserves the right to change the contents of this document as necessary.

Revision: 130527
Revision Date: 27.05.2013